## **Model MRMS**

### Multi-Room Monitoring Station





#### **DESCRIPTION**

The MRMS (Multi-Room Monitoring Station) is designed for installation in a central location, such as a nurses station or main control room. It is designed to be flush mounted to provide remote viewing and alarm monitoring for up to 8 rooms or critical spaces equipped with Setra's Pressure and Room Condition Monitors, such as the Model SRPM or SRCM. The built-in Auto-Discover feature will automatically search and connect to other SRPM and SRCM units through BACnet® MS/TP and import all MAC addresses, BACnet objects, naming conventions and other setup parameters. A built-in audible and visual alarm and high definition color display alerts users to room status and room condition, while allowing for easy alert of a change in room condition.

#### **FEATURES**

- Remotely Monitor up to 8 Rooms
- Auto-Discover
- Built-in Audible & Visual Alarm
- Display Room Status and Room Condition
- Flush Mount Design
- Easy Installation
- Reduce Total Installation Cost
- BACnet® MS/TP Protocol
- High Definition Color (TFT) Touchscreen Display
- Meets CE Conformance Standards

#### **APPLICATIONS**

- Nurses Station
- Surgical Suites
- Intensive Care Isolation Rooms
- Pharmacology
- Research Laboratories
- Pharmaceutical Manufacturing
- Clean Rooms
- Biological Safety Lab
- Animal Research Vivarium
- Organic Laboratory


SPECIFICATIONS									
Physical Description		Environmental Data		Electrical Data (Voltage)					
Case	Fire Retardant Plastic UL94V-0	Operating Temperature <sup>3</sup> °F (°C)	32 to +120 (0 to +50)	Power Input	18-32 VAC, 50-60Hz				
Dimensions)	5.84"H x 7.45"W x 0.38"D	Storage Temperature °F (°C)	-20 to +160 (-30 to +170)	Power Consumption	10W				
Electrical Connection	Removable Terminal Block	Operating Humidity	5 to 95% RH (Non-Condensing)	Circuit	2-Wire (Exc, Com)				
Weight	1 ib. 2 oz. (482 grams)	Communications		Certifications					
Mounting	Standard Triple Gang Double-Deep-Elec- trical Box	BACnet®	MS/TP ASC	Œ	Conforms to European Pressure Directive				
Display	Touchscreen LCD 4.3″TFT, 480 x 272			CSA	CAN/CSA - C22.2 No. 61010-1-04 ANSI/UL 61010-1, 3rd Edition				


Specifications subject to change without notice



# **Model MRMS**

### Multi-Room Monitoring Station





ORDERING INFORMATION						
M R M S	-				CCD MADMAC Dox	
Model	Face Plate Logo		Logo	<b>⊚</b> BACnet°		
MRMS = MRMS	Std.	S	Setra	"BACnet" is a registered trademark of ASHRAF"		
	Opt.	В	Blank/No Logo	Ordering Example: MRMSS = Model MRMS with Setra logo on Face Plate.		